



Main

Range	Square D X Series
Product or Component Type	Cover frame
Accessory / separate part category	Installation accessory
Aesthetic name	X Series
Number of gangs	1 gang
Product destination	Switch Dimmer Socket-outlet Sensor Fan controller USB charger + socket-outlet
Color	Black

Complementary

Suitable for body type	Decorator
Fixing Mode	Screwless
Material	Plastic
Surface treatment	Painted
Surface Finish	Matte
Height	4.72 in (120 mm)
Width	2.76 in (70 mm)
Depth	0.28 in (7 mm)
Quantity per Set	1 piece

Environment

Product Certifications	cULus
Standards	UL 514D

Ordering and shipping details

Category	09936-WD AESTHETIC WALL PLATES
Discount Schedule	DE9
GTIN	785901550938
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.28 in (0.7 cm)
Package 1 Width	2.76 in (7.0 cm)
Package 1 Length	4.72 in (12.0 cm)
Package 1 Weight	1.09 oz (31.0 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	3.94 in (10.0 cm)

Package 2 Width	3.54 in (9.0 cm)
Package 2 Length	5.31 in (13.5 cm)
Package 2 Weight	13.51 oz (383.0 g)
Unit Type of Package 3	CAR
Number of Units in Package 3	200
Package 3 Height	11.42 in (29.0 cm)
Package 3 Width	8.46 in (21.5 cm)
Package 3 Length	18.70 in (47.5 cm)
Package 3 Weight	19.09 lb(US) (8.66 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: carbon black, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	2 years
----------	---------