

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2018





© COPYRIGHT 2018

BY TYCO ELECTRONICS JAPAN G.K.

ALL RIGHTS RESERVED.

REVISIONS




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCT RELEASE	23JUL2018	M. J	E. I

3-2326092-2
(KEYING:XY)2-2326092-2
(KEYING:YY)1-2326092-2
(KEYING:XX)

COMPANY LOGO

SERIES MARK


CIRCUIT NO

RECOMMENDED PCB HOLE PATTERN (TOLERANCE: ±0.05)
RECOMMENDED PCB THICKNESS: 1.6~2.4±0.1
(CONNECTOR MOUNT SIDE)

XY			3-2326092-2
YY			2-2326092-2
XX			1-2326092-2
KEY TYPE	FINISH	PART NO.	

1. MATERIAL:
HOUSING: GLASS FILLED THERMO PLASTICS, POLYESTER(94V-0),
COLOR: BLACK.
TAB CONTACT: COPPER ALLOY.
RETENTION LEG: BRASS.

- FINISH(CONTACT AREA): 0.38um MIN Au PLATING OVER Ni PLATING.
 FINISH(CONTACT TAIL, RETENTION LEG): Sn PLATING OVER Ni PLATING.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. JIANG 23JUL2018	TE Connectivity NAME VERTICAL HDR, DOUBLE ROW, 6 POS DYNAMIC D5200				
DIMENSIONS: mm		CHK T. SHIMOYASU 23JUL2018					
		APVD F. IKEMATSU 23JUL2018					
		PRODUCT SPEC 108-5453					
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.3 1 PLC ±0.3 2 PLC ±0.3 3 PLC ±0.3 4 PLC ±0.3 ANGLES ±3°		APPLICATION SPEC -	SIZE A3		CAGE CODE 00779	DRAWING NO C-2326092	RESTRICTED TO -
		WEIGHT -					
MATERIAL SEE NOTE		FINISH SEE NOTE	CUSTOMER DRAWING				
			SCALE		SHEET	OF	REV A