

D

C

B

A

4

3

2

1

|                              |  |                          |  |                      |
|------------------------------|--|--------------------------|--|----------------------|
| THIS DRAWING IS UNPUBLISHED. |  | RELEASED FOR PUBLICATION |  | 20                   |
| © COPYRIGHT 20               |  | BY -                     |  | ALL RIGHTS RESERVED. |





| REVISIONS |     |                 |           |     |      |
|-----------|-----|-----------------|-----------|-----|------|
| P         | LTR | DESCRIPTION     | DATE      | DWN | APVD |
|           | A   | INITIAL RELEASE | 02JUN2015 | DL  | CW   |
|           | A1  | ECR-18-004153   | 08AUG2018 | GY  | CW   |
|           | B   | ECR-21-109004   | 13AUG2021 | WQR | CW   |
|           |     |                 |           |     |      |

D

C


B

A



TYPE 1: SIDE ENTRY  
类型1：侧出


PG/M THREAD 2  
PG/M螺纹孔 2



TYPE 2: TOP ENTRY, UNDEFINED DIMENSIONS REFER TO TYPE 1.  
类型2：顶出，未定义尺寸&规格参照类型1。

PG/M THREAD 1  
PG/M螺纹孔 1

PG/M THREAD 1  
PG/M螺纹孔 1




TYPE 3: SIDE/TOP ENTRY, UNDEFINED DIMENSIONS REFER TO TYPE 1.  
类型3：侧/顶出，未定义尺寸&规格参照类型1。


NOTES:  
1. TECHNICAL CHARACTERISTICS:  
BODY MATERIAL: DIE CAST ALUMINIUM ALLOY  
SURFACE TREATMENT: POWDER-COATED, GRAY  
DEGREE OF PROTECTION: IP65 (MATED)

注释:  
1. 技术参数:  
主体材料: 铝合金  
表面处理: 粉末喷涂, 灰色  
防护等级: IP65(配合)


|                   |                        |                                                                                         |                           |                           |               |
|-------------------|------------------------|-----------------------------------------------------------------------------------------|---------------------------|---------------------------|---------------|
| T1310320121-000   | H32B-TS-RO-PG21        | H32B HOOD, SIDE ENTRY PG21, 2 EAR, POWDER COATED, GREY<br>H32B上壳, 侧出PG21, 2耳, 灰色粉末喷涂    | PG21                      | -                         | TYPE 1<br>类型1 |
| T1310320129-000   | H32B-TS-RO-PG29        | H32B HOOD, SIDE ENTRY PG29, 2 EAR, POWDER COATED, GREY<br>H32B上壳, 侧出PG29, 2耳, 灰色粉末喷涂    | PG29                      | -                         |               |
| T1310320132-000   | H32B-TS-RO-M32         | H32B HOOD, SIDE ENTRY M32, 2 EAR, POWDER COATED, GREY<br>H32B上壳, 侧出M32, 2耳, 灰色粉末喷涂      | M32                       | -                         |               |
| T1310320136-000   | H32B-TS-RO-PG36        | H32B HOOD, SIDE ENTRY PG36, 2 EAR, POWDER COATED, GREY<br>H32B上壳, 侧出PG36, 2耳, 灰色粉末喷涂    | PG36                      | -                         |               |
| T1310320140-000   | H32B-TS-RO-M40         | H32B HOOD, SIDE ENTRY M40, 2 EAR, POWDER COATED, GREY<br>H32B上壳, 侧出M40, 2耳, 灰色粉末喷涂      | M40                       | -                         |               |
| T1320320121-000   | H32B-TG-RO-PG21        | H32B HOOD, TOP ENTRY PG21, 2 EAR, POWDER COATED, GREY<br>H32B上壳, 顶出PG21, 2耳, 灰色粉末喷涂     | -                         | PG21                      | TYPE 2<br>类型2 |
| T1320320125-000   | H32B-TG-RO-M25         | H32B HOOD, TOP ENTRY M25, 2 EAR, POWDER COATED, GREY<br>H32B上壳, 顶出M25, 2耳, 灰色粉末喷涂       | -                         | M25                       |               |
| T1320320129-000   | H32B-TG-RO-PG29        | H32B HOOD, TOP ENTRY PG29, 2 EAR, POWDER COATED, GREY<br>H32B上壳, 顶出PG29, 2耳, 灰色粉末喷涂     | -                         | PG29                      |               |
| T1320320132-000   | H32B-TG-RO-M32         | H32B HOOD, TOP ENTRY M32, 2 EAR, POWDER COATED, GREY<br>H32B上壳, 顶出M32, 2耳, 灰色粉末喷涂       | -                         | M32                       |               |
| T1320320136-000   | H32B-TG-RO-PG36        | H32B HOOD, TOP ENTRY PG36, 2 EAR, POWDER COATED, GREY<br>H32B上壳, 顶出PG36, 2耳, 灰色粉末喷涂     | -                         | PG36                      |               |
| T1320320140-000   | H32B-TG-RO-M40         | H32B HOOD, TOP ENTRY M40, 2 EAR, POWDER COATED, GREY<br>H32B上壳, 顶出M40, 2耳, 灰色粉末喷涂       | -                         | M40                       |               |
| T1320320142-000   | H32B-TG-RO-PG42        | H32B HOOD, TOP ENTRY PG42, 2 EAR, POWDER COATED, GREY<br>H32B上壳, 顶出PG42, 2耳, 灰色粉末喷涂     | -                         | PG42                      |               |
| T1320320150-000   | H32B-TG-RO-M50         | H32B HOOD, TOP ENTRY M50, 2 EAR, POWDER COATED, GREY<br>H32B上壳, 顶出M50, 2耳, 灰色粉末喷涂       | -                         | M50                       |               |
| T1320320163-000   | H32B-TG-RO-M63         | H32B HOOD, TOP ENTRY M63, 2 EAR, POWDR COATED, GREY<br>H32B上壳, 顶出M63, 2耳, 灰色粉末喷涂        | -                         | M63                       | TYPE 3<br>类型3 |
| T1320320225-000   | H32B-TG-RO-2M25        | H32B HOOD, SIDE/TOP ENTRY M25, 2 EAR, POWDER COATED, GREY<br>H32B上壳, 侧顶出M25, 2耳, 灰色粉末喷涂 | M25                       | M25                       |               |
| PART NUMBER<br>料号 | PART DESCRIPTION<br>描述 |                                                                                         | PG/M THREAD 1<br>PG/M螺纹孔1 | PG/M THREAD 2<br>PG/M螺纹孔2 | TYPE<br>类型    |

|                                                                                       |  |                          |                                                                                                       |  |       |
|---------------------------------------------------------------------------------------|--|--------------------------|-------------------------------------------------------------------------------------------------------|--|-------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  | DWN DAVID LI 02JUN2015   |  TE Connectivity |  |       |
| DIMENSIONS:<br>mm                                                                     |  | CHK CHRIS WANG 02JUN2015 |                                                                                                       |  |       |
|  |  | APVD XU XIANG 02JUN2015  | NAME H32B-TS/TG/TSH/TGH-RO-M/PG                                                                       |  |       |
|                                                                                       |  | PRODUCT SPEC             | 108-137013                                                                                            |  |       |
| TOLERANCES UNLESS OTHERWISE SPECIFIED:                                                |  | APPLICATION SPEC         | 114-137013                                                                                            |  |       |
| MATERIAL                                                                              |  | WEIGHT                   | A200779                                                                                               |  |       |
| FINISH                                                                                |  | CUSTOMER DRAWING         | C-T13X0320XXX000                                                                                      |  |       |
|                                                                                       |  | SCALE 1:1                | SHEET 1 OF 2                                                                                          |  | REV B |



| REVISIONS |     |             |      |     |      |
|-----------|-----|-------------|------|-----|------|
| P         | LTR | DESCRIPTION | DATE | DWN | APVD |
|           |     | SEE SHEET I |      |     |      |
|           |     |             |      |     |      |
|           |     |             |      |     |      |
|           |     |             |      |     |      |




PG/M THREAD 4  
PG/M 螺纹孔 4



TYPE 4: HIGH CONSTRUCTION, SIDE ENTRY, UNDEFINED DIMENSIONS REFER TO TYPE 1.  
类型4: 高结构, 侧出, 未定义尺寸&规格参照类型1.



TYPE 5: HIGH CONSTRUCTION, TOP ENTRY, UNDEFINED DIMENSIONS REFER TO TYPE 4.  
类型5: 高结构, 顶出, 未定义尺寸&规格参照类型4.

|                                                                                       |  |                                        |                                |                               |                                                                                                       |                                                  |  |        |  |     |  |
|---------------------------------------------------------------------------------------|--|----------------------------------------|--------------------------------|-------------------------------|-------------------------------------------------------------------------------------------------------|--------------------------------------------------|--|--------|--|-----|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  |                                        | DWN<br>DAVID LI<br>02JUN2015   |                               |  TE Connectivity |                                                  |  |        |  |     |  |
|                                                                                       |  |                                        | CHK<br>CHRIS WANG<br>02JUN2015 |                               |                                                                                                       |                                                  |  |        |  |     |  |
| DIMENSIONS:<br>mm                                                                     |  | TOLERANCES UNLESS OTHERWISE SPECIFIED: |                                | APVD<br>XU XIANG<br>02JUN2015 |                                                                                                       | NAME<br>H32B-TS/TG/TSH/TGH-RO-M/PG               |  |        |  |     |  |
|  |  | 0 PLC ±·                               |                                | PRODUCT SPEC                  |                                                                                                       | SIZE<br>CAGE CODE<br>DRAWING NO<br>RESTRICTED TO |  |        |  |     |  |
|                                                                                       |  | 1 PLC ±·                               |                                | 108-137013                    |                                                                                                       |                                                  |  |        |  |     |  |
|                                                                                       |  | 2 PLC ±·                               |                                | APPLICATION SPEC              |                                                                                                       |                                                  |  |        |  |     |  |
|  |  | 3 PLC ±·                               |                                | 114-137013                    |                                                                                                       | A200779C=T13X0320XXX000                          |  |        |  |     |  |
|                                                                                       |  | 4 PLC ±·                               |                                | WEIGHT                        |                                                                                                       |                                                  |  |        |  |     |  |
|                                                                                       |  | ANGLES ±·                              |                                | -                             |                                                                                                       |                                                  |  |        |  |     |  |
| MATERIAL                                                                              |  | FINISH                                 |                                | CUSTOMER DRAWING              |                                                                                                       | SCALE                                            |  | SHEET  |  | REV |  |
| -                                                                                     |  | -                                      |                                |                               |                                                                                                       | 1:1                                              |  | 2 OF 2 |  | B   |  |
| -                                                                                     |  | -                                      |                                |                               |                                                                                                       |                                                  |  |        |  |     |  |