









POLARIZATION KEYS			
TYPE "A"	TYPE "B"	TYPE "C"	TYPE "D"
P / N 293593-1 AS SHOWN	P / N 293593-2 AS SHOWN	P / N 293593-3 AS SHOWN	P / N 293593-4 AS SHOWN
			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±°
1 PLC	±0.3
2 PLC	±0.20
3 PLC	±°
4 PLC	±°
ANGLES	±3°

MATERIAL

-

FINISH

-

DWN

M. ZUCCA

30OCT2009

CHK

M. ZUCCA

30OCT2009

APVD

G. TURCO

30OCT2009

PRODUCT SPEC

108-20304

APPLICATION SPEC

114-20152

WEIGHT

-

Customer Drawing

TE Connectivity

NAME

PIN CONNECTOR
PCB STRAIGHT VERSION
NECTOR* M-LINE

SIZE

CAGE CODE

DRAWING NO

A300779

C-293593

RESTRICTED TO

-

SCALE

2:1

SHEET

2

OF

3

REV

F2

1470-19 (3/11)

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2011

© COPYRIGHT 2011

BY -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR


DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1




PCB TOP VIEW


PCB BOTTOM VIEW

SUGGESTED L, N AND PE TRACKS LAYOUT ON PCB


- TOP VIEW -



- BOTTOM VIEW -



SUGGESTED PCB LAYOUT CUT-OUT



SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN M. ZUCCA 30OCT2009

CHK M. ZUCCA 30OCT2009

APVD G. TURCO 30OCT2009

PRODUCT SPEC

108-20304

APPLICATION SPEC


114-20152

WEIGHT -

Customer Drawing

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

- 0 PLC ±0.3
- 1 PLC ±0.20
- 2 PLC ±0.20
- 3 PLC ±0.20
- 4 PLC ±0.20
- ANGLES ±3°

MATERIAL

-

FINISH

-



TE Connectivity

NAME
PIN CONNECTOR
PCB STRAIGHT VERSION
NECTOR* M-LINE

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A300779C-293593

SCALE 3:1 SHEET 3 OF 3 REV F2