





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E2	REVISED PER ECR-17-013073	14SEP2017	JH	PKS

1. SPECIFICATIONS:
MAGNET WIRE #27 - #36 AWG,
0.38mm (.015") - 0.13 (.005") DIA. COPPER
OTHER SIZES MAY BE ACCOMMODATED,
CONSULT TYCO ELECTRONICS FOR APROVAL.
2. POCKET RECOMMENDATION: #1601424
- 3

 TERMINAL APPLICATION TO COMPLY WITH
TYCO ELECTRONICS SPECIFICATION 114-13166
FIGURE 5.



OBSOLETE	SELECTIVE TIN PLATE OVER NICKEL	---	4-1601120-4
	SELECTIVE POST TIN LEAD PLATE OVER NICKEL	050-011-119	4-1601120-2
	SELECTIVE TIN PLATE OVER NICKEL	---	2-1601120-4
	SELECTIVE POST TIN LEAD PLATE OVER NICKEL	150-012-119	2-1601120-2
OBSOLETE	UNPLATED	150-012-000	2-1601120-1
SUPERSEDED	SELECTIVE TIN PLATE OVER NICKEL	---	1601120-4
	SELECTIVE POST TIN LEAD PLATE OVER NICKEL	150-011-019	1601120-3
OBSOLETE	SELECTIVE POST TIN LEAD PLATE OVER NICKEL	150-011-119	1601120-2
	UNPLATED	150-011-000	1601120-1
FINISH		REFERENCE P/N	TYCO PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.WELLER 11JAN2002 CHK M.FEHER 11JAN2002 APVD K.RANDOLPH 11JAN2002	NAME
DIMENSIONS: INCHES		PRODUCT SPEC 108-2244	APPLICATION SPEC
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .01[0.25] 3 PLC ± .005[0.13] 4 PLC ± - ANGLES ± 2°		FINISH	SEE TABLE
MATERIAL BRASS, SPRING HARD		WEIGHT 0.000000	CUSTOMER DRAWING
		SCALE 1:3	SHEET 1 of 1
		REV E2	