

SUMMARY

Wires

Low voltage	4
Coax	1



Image is for illustrative purpose only

Series	2P
Termination type	Male crimp mixed / multi coax
IP rating	50
AWG wire size	30.00 - 22.00
Cable Ø	0.00 - 0.00 mm
Status	active

Download

[Request a quote](#)

[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model	CL*: Fixed receptacle, nut fixing
Keying	3 keys (alpha=0, gamma=60; Plug: male contacts; Receptacle: female contacts)
Housing Material	PSU (Polysulfone), gray
Weight	6.12 g

Performance

Configuration	2P.804 : 1 Coax (50 Ohm), 4 Low V.
Insulator	L: PEEK for solder contacts
Rated Current	5 Amps

Specifications


Test voltage (kV rms) Contact-contact:	0.85
Air clearance min.:	0.6 mm
Creepage distance min.:	0.6 mm

Others

Endurance (Shell):	>1000 mating cycles
Temp (min / max):	-50°C / +150°C

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

DRAWINGS



Dimensions

	N
mm.	23.8
in.	0,94

RECOMMENDED BY LEMO

Tools

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.