




47.3	45.3	9
42.3	40.3	8
37.3	35.3	7
32.3	30.3	6
27.3	25.3	5
22.3	20.3	4
17.3	15.3	3
12.3	10.3	2
B	A	NO. OF POS.






DIMENSIONS: mm/IN [CHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		DWN 02MAR2004 FLAIG CHY 02MAR2004 HUMMEL APR 02MAR2004 HUMMEL		Tyco Electronics Tyco Electronics Harrisburg, PA 17105-3608	
		0 PLC ± 1 PLC ± 2 PLC ±0.25(.010) 3 PLC ± 4 PLC ± ANGLES ± FINISH ±0.2		PRODUCT SPEC DIN-253 APPLICATION SPEC		NAME ASSEMBLY, DIN, RAST 5, HEADER, VERTICAL - - -	
MATERIAL 5		FINISH 6		WEIGHT -		SIZE CAGE CODE DRAWING NO A 00779 C=521383	
				CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 3 REV C	

[illegible]

1-2, 3-4, 5-6	1c, 3c, 6d	1b, 2a, 3a, 4b 5a, 5b, 6b	6	-	 2-521383-6
2-3, 7-8	2c, 8d	3b, 8a	9	-	 3-521383-9
1-2, 4-5, 6-7, 8-9	1c, 2d, 7d, 8c	1b, 2a, 4b, 5a, 8b, 9b	9	-	 2-521383-9
1-2, 6-7	3d, 7d	5b	9	09-D	 1-521383-9
2-3, 7-8	2c, 8d	2b, 5a	9	09-C +2c	 521383-9
2-3, 7-8	2c, 3d, 7c	8b	8	08-C	2-521383-8
1-2, 3-4, 5-6 7-8	3c, 6d	4a, 6b	8	-	1-521383-8
1-2, 7-8	2d, 3c, 6d, 7c	-	8	08-D	521383-8
1-2, 5-6	3d, 7d	3a, 4a	7	-	3-521383-7
1-2, 5-6	3c, 4d, 7c	1a, 6b	7	-	2-521383-7
1-2, 4-5, 6-7	3c, 5d, 6c, 7d	1a, 2a, 4a, 4b, 5b, 6a, 6b, 7b	7	-	1-521383-7
1-2, 6-7	3d, 7d	5b	7	07-C	521383-7
1-2, 5-6	4d	2b, 6b	6	06-D	1-521383-6
1-2, 4-5	3c, 6d	1b	6	06-A	521383-6
1-2, 3-4	1c, 2d, 3c, 5d	1a, 5b	5	-	3-521383-5
2-3	3d, 4c	1a, 5b	5	-	2-521383-5
1-2, 3-4	2d, 5d	2b	5	-	1-521383-5
1-2, 4-5	2d	2b	5	05-B	521383-5
1-2, 3-4	1c, 2d, 3c, 4d	2a, 3a, 3b, 4b	4	-	 8-521383-4
1-2, 3-4	1c, 2d, 3c, 4d	1b, 2a, 4b	4	-	 7-521383-4
1-2, 3-4	1c, 3c, 4d,	1b, 2b, 3b, 4a	4	-	 6-521383-4
1-2, 3-4	2d, 3c	1b, 2a, 2b, 3b, 4b	4	-	5-521383-4
1-2, 3-4	2d	2a, 4b	4	04-G	4-521383-4
1-2, 3-4	4d	1a, 3a	4	04-F	3-521383-4
1-2, 3-4	4d	1a, 4b	4	04-C	2-521383-4
1-2, 3-4	1c	1a, 4b	4	04-B	1-521383-4
1-2, 3-4	3c, 4d	1b	4	04-A	521383-4
2-3	1d, 3d	3b	3	-	3-521383-3
1-2	3c	1a	3	03-D	2-521383-3
2-3	1d, 2c	2b, 3b	3	03-B	1-521383-3
1-2	1c, 2d	1b	3	03-A	521383-3
1-2	1c, 2d	2b	2	02-P	6-521383-2
1-2	1c	1b, 2b	2	02-I	5-521383-2
1-2	2d	1b, 2a, 2b	2	02-G	4-521383-2
1-2	2d	1a, 2b	2	02-E	3-521383-2
1-2	1c, 2d	2a	2	02-C	2-521383-2
1-2	1c	1a, 2b	2	02-B	1-521383-2
1-2	1c, 2d	1b, 2a	2	02-A	521383-2
LATCH WINDOWS	KEYING	POLAR.	NO. OF POS.	RAST 5 DESIG.	PART NUMBER

101. DRAWING IS A CONTROLLING DOCUMENT FOR THIS ELECTRONIC COMPONENT 102. THIS DRAWING IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION 103. IT IS TO BE KEPT IN CONFIDENCE AND NOT TO BE REPRODUCED OR COPIED 104. IT IS TO BE DESTROYED WHEN NO LONGER REQUIRED		DWN 02MAR2004 CHG 02MAR2004 1 HUMMEL APD 02MAR2004 1 HUMMEL		Tyco Electronics Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME ASSEMBLY, DIN, RAST 5, HEADER, VERTICAL -	
		0 PLC ±.1 1 PLC ±.1 2 PLC ±.05 [.010] 3 PLC ±.1 4 PLC ±.1 ANGLES ±.2°		PRODUCT SPEC 108-2183 APPLICATION SPEC	
MATERIAL -		FINISH -		SIZE CAGE CODE DRAWING NO A 00779 C=521383	
WEIGHT -		CUSTOMER DRAWING		SCALE 4:1 SHEET 2 OF 3 REV C	

LOC	DIST	REVISIONS			
AF	50	P	LYR	DESCRIPTION	DATE
		-	-	SEE SHEET 1	-



PICTORIAL VIEW KEY

THIS DRAWING IS UNPUBLISHED. IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS TO BE USED ONLY FOR THE PURPOSES SPECIFIED BY THE DRAWING. IT IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM. WITHOUT PERMISSION IN WRITING FROM TYCO ELECTRONICS CORPORATION, ALL RIGHTS ARE RESERVED.		DWN R. FLAG 02MAR2004	Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK J. HUMMEL 02MAR2004	NAME ASSEMBLY, DIN, RAST 5, HEADER, VERTICAL	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. HUMMEL 02MAR2004	SIZE A1	
9 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		± ± ± ± ±2° -	CAGE CODE 00779	
MATERIAL -		WEIGHT -	DRAWING NO. C=521383	
CUSTOMER DRAWING		SCALE 4:1	SHEET 3	REV C5