




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	21MAY2015	GY	CW
	A1	ECR-18-009564	14SEP2018	CD	CW
	B	ECR-20-011774	30APR2021	BS	CW

D


printed on 30 Apr 2021 15:24 (China Standard Time) from IE236667

A



NOTES:
1. TECHNICAL CHARACTERISTICS:
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE TREATMENT: SEE TABLE
DEGREE OF PROTECTION: IP68 (MATED)

注释
1. 技术参数:
壳体材料: 铝合金
表面处理: 见表格
防护等级: IP68 (配合)




D

C


B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN 21MAY2015 Gino Yao		 TE Connectivity		
			CHK 21MAY2015 Chris Wang				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 21MAY2015 Xiang Xu		NAME H6BPR-TSHC-PG/M	
		0 PLC ±-		PRODUCT SPEC		SIZE A2	
		1 PLC ±-		108-137014			
		2 PLC ±-		APPLICATION SPEC			
		3 PLC ±-		114-137014			
4 PLC ±-				WEIGHT		CAGE CODE	
4 ANGLES ±-				-		DRAWING NO	
MATERIAL		FINISH				RESTRICTED TO	
-		-				-	
Customer Drawing						SCALE 1:1	
						SHEET 1 OF 2	
						REV B	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

TYPE 2:NO LOGO
类型：无LOGO



THIS TYPE IS SAME AS TYPE I, ONLY NO LOGO
此类型同类型I，只是无LOGO

T1912062125-001	POWDER COATED, DEEP GRAY 表面喷涂, 深灰色	H6BPR-TSHC-M25	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY M25,POWDER COATED,DEEP GREY,NO LOGO H6BPR上壳,中部锁定,侧出M25,深灰色粉末喷涂,无LOGO	M25	TYPE 2 类型2
T1912062125-000	POWDER COATED, GRAY 表面喷涂, 灰色	H6BPR-TSHC-M25	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY M25,POWDER COATED,GRAY H6BPR上壳,中部锁定,侧出M25,灰色粉末喷涂	M25	TYPE 1 类型1
T1912062121-000	POWDER COATED, GRAY 表面喷涂, 灰色	H6BPR-TSHC-PG21	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY PG21,POWDER COATED,GRAY H6BPR上壳,中部锁定,侧出PG21,灰色粉末喷涂	PG21	
T1912062120-000	POWDER COATED, GRAY 表面喷涂, 灰色	H6BPR-TSHC-M20	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY M20,POWDER COATED,GRAY H6BPR上壳,中部锁定,侧出M20,灰色粉末喷涂	M20	
T1912062116-000	POWDER COATED, GRAY 表面喷涂, 灰色	H6BPR-TSHC-PG16	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY PG16,POWDER COATED,GRAY H6BPR上壳,中部锁定,侧出PG16,灰色粉末喷涂	PG16	
T1912061125-000	POWDER COATED, SILVER WHITE 表面喷涂, 银白色	H6BPR-TSHC-M25	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY M25,POWDER COATED,SILVER WHITE H6BPR上壳,中部锁定,侧出M25,银白色粉末喷涂	M25	
T1912061121-000	POWDER COATED, SILVER WHITE 表面喷涂, 银白色	H6BPR-TSHC-PG21	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY PG21,POWDER COATED,SILVER WHITE H6BPR上壳,中部锁定,侧出PG21,银白色粉末喷涂	PG21	
T1912061120-000	POWDER COATED, SILVER WHITE 表面喷涂, 银白色	H6BPR-TSHC-PG21	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY M20,POWDER COATED,SILVER WHITE H6BPR上壳,中部锁定,侧出M20,银白色粉末喷涂	M20	
T1912061116-000	POWDER COATED, SILVER WHITE 表面喷涂, 银白色	H6BPR-TSHC-PG16	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY PG16,POWDER COATED,SILVER WHITE H6BPR上壳,中部锁定,侧出PG16,银白色粉末喷涂	PG16	
T1912060125-000	POWDER COATED, BLACK 表面喷涂, 黑色	H6BPR-TSHC-M25	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY M25,POWDER COATED,BLACK H6BPR上壳,中部锁定,侧出M25,黑色粉末喷涂	M25	
T1912060121-000	POWDER COATED, BLACK 表面喷涂, 黑色	H6BPR-TSHC-PG21	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY PG21,POWDER COATED,BLACK H6BPR上壳,中部锁定,侧出PG21,黑色粉末喷涂	PG21	
T1912060120-000	POWDER COATED, BLACK 表面喷涂, 黑色	H6BPR-TSHC-M20	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY M20,POWDER COATED,BLACK H6BPR上壳,中部锁定,侧出M20,黑色粉末喷涂	M20	
T1912060116-000	POWDER COATED, BLACK 表面喷涂, 黑色	H6BPR-TSHC-PG16	H6BPR HOOD,CENTER LOCKING,SIDE ENTRY PG16,POWDER COATED,BLACK H6BPR上壳,中部锁定,侧出PG16,黑色粉末喷涂	PG16	
PART NUMBER 料号	SURFACE TREATMEN 表面处理	PART DESCRIPTION 描述		PG/M THREAD PG/M 螺纹	TYPE 类型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 21MAY2015 Gino.Yao CHK 21MAY2015 Chris.Wang APVD 21MAY2015 Xiang.Xu		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		H6BPR-TSHC-PG/M	
MATERIAL		PRODUCT SPEC 108-137014 APPLICATION SPEC 114-137014		SIZE	RESTRICTED TO
-		WEIGHT		CAGE CODE	
-		-			DRAWING NO
		Customer Drawing			T191206XXXXX00
				SCALE	SHEET
				1:1	2 OF 2
				REV	B