



Pushing Performance  
Since 1945

# har-port USB 2.0 A-A, PFT



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 452 1901
Specification	har-port USB 2.0 A-A, PFT
HARTING eCatalogue	<a href="https://b2b.harting.com/09454521901">https://b2b.harting.com/09454521901</a>

## Identification

Category	Connectors
Series	har-port
Element	Service interfaces
Specification	USB 2.0

## Version

Connection type	Type A jack - type A jack
Fixing	Screwable in cover plates

## Technical characteristics

Ambient temperature	-25 ... +70 °C
Mating cycles	≥1,500
Degree of protection acc. to IEC 60529	IP20

## Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	Silver
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide
	Lead
	Nickel
	Naphthalene

## Specifications and approvals

Specifications	EN 45545-2
UL / CSA	UL 1863 DUXR2.E470046
	CSA-C22.2 No. 182.4, No. 233-09 DUXR8.E470046
Approvals	DNV GL

## Commercial data

Packaging size	1
Net weight	10 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140060463
ETIM	EC002599
eCl@ss	27060304 Appliance cord (data cable)