

[Home](#)[About Us](#)[Investor Relations](#)[Where To Buy](#)[News](#)[Events](#)[Contact Us](#)[Log In](#)Search For [Part Number](#)[Home](#) > 5500205100FPart Number: **5500205100F****General Description**

Series	550
Configuration	5 mm Lens
Description	5 mm CBI
Package Options	Bulk Packaging
Sizes	5mm
Lamp Type	Single Color
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Diffused
LED Centerline	3.00

Absolute Maximum Ratings (Ta = 25°)

Forward Current mA	30mA
Reverse Current	100 @ Vr = 5V
Derating	from 25° @ .4 mA/°C
Solder Temperature	260° for 5 sec
Operating Temperature	-55 to +100
Storage Temperature	-55 to +100



5500205100F

[check stock](#)

This is a
RoHS Compliant Product
[To learn more click here](#)

Operating Characteristics

Color	<div><div></div></div> Green
LED Type	Standard Efficiency
Luminous Intensity Min	3.5
Luminous Intensity Typical	12.3
Test Current mA	20mA
Emitted Color	Green
Power Dissipation Max	100mW

[Site Map](#) [Contact Us](#) [Dialight BLP Ltd](#) [Privacy Policy](#) [Careers](#)

Copyright© 2009, Dialight. All Rights Reserved.

