

## Coaxial Panel Connector 22\_N-50-0-23/133\_N

### Description

Straight bulkhead receptacle jack

Interface standards

IEC 61169-16\_MIL-STD-348A/304\_CECC 22210



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	11 GHz

#### Mechanical Data

Number of matings	500
Weight	0.0208 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

### Related Documents

Outline drawing	DOU-00011222
Catalogue drawing	DCA-00011224

### Ordering Information

Bulk 50 pcs package	22_N-50-0-23/133_NF
---------------------	---------------------