

## Coaxial PCB Connector 82\_MMBX-50-0-4/111\_N

### Description

Straight PCB jack

Interface Standards  
SUHNER-MMBX



### Technical Data

#### Electrical Data

|                          |             |
|--------------------------|-------------|
| Impedance                | 50 $\Omega$ |
| Interface frequency max. | 12.4 GHz    |

#### Mechanical Data

|                     |               |
|---------------------|---------------|
| Board mounting type | through holes |
| Weight              | 0.000675 kg   |

#### Environmental Data

|  |                  |
|--|------------------|
| Operating temperature                                | -55 °C to 155 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant        |

#### Material Data

| Piece Parts    | Material                     | Surface Plating |
|----------------|------------------------------|-----------------|
| Centre contact | Brass                        | SUCOPRO Plating |
| Outer contact  | Brass                        | SUCOPRO Plating |
| Body           | Brass                        | SUCOPRO Plating |
| Insulator      | LCP (Liquid crystal polymer) |                 |

### Related Documents

|                   |              |
|-------------------|--------------|
| Outline drawing   | DOU-00012724 |
| Catalogue drawing | DCA-00087582 |
| Mounting hole     | DOU-00002008 |

### Ordering Information

|                      |                       |
|----------------------|-----------------------|
| Bulk 100 pcs package | 82_MMBX-50-0-4/111_NH |
|----------------------|-----------------------|

### Remarks

PCB connector with stand-offs