

Between Series Adaptor 33_SK-MMPX-50-1/199_N

Description

Adaptor plug/jack
SK plug (male) / MMPX jack (female)

Precision adaptor
For Test & Measurement applications

Interface standards
Series SK - MIL-STD-348A/323
Series MMPX - HUBER+SUHNER MMPX STD (Patent US 7.294.023)



Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	40 GHz		
Frequency range	DC to 15 GHz	15 to 30 GHz	30 to 40 GHz
Return loss	≥ 26 dB	≥ 23 dB	≥ 20 dB
Electrical length	16.1 mm		

Mechanical Data

Number of matings	100
Weight	0.0039 kg

Environmental Data

Operating temperature	-40 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - SK plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PPE (Polyphenylene ether, PPO)	
Coupling nut	Stainless Steel	

Interface - MMPX jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Copper Beryllium Alloy	
Body	Stainless Steel	
Insulator	PPE (Polyphenylene ether, PPO)	

Related Documents

Outline drawing	DOU-00128127
-----------------	--------------

Ordering Information

Single package	33_SK-MMPX-50-1/199_NE
----------------	------------------------