






REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C190323	2019/03/04	Vicky	Change Note




Recommended Panel
Cut-Out





AAD-XXPMMS-LC7001

02:2Pin
03:3Pin



△Note:

- * Ⓞ Important Dimension To Check.
- * Waterproof Rate: IP67, Unmated.
- * Housing: Thermoplastic, Black.
- * Pin: Copper Alloy, Gold Plated.
- * Nut: Thermoplastic, Black.
- * Gasket: Rubber, Gray.
- * Use with waterproof cap or dust cap
Maximum Panel Thickness: 2.3mm
- * Use without waterproof cap or dust cap
Maximum Panel Thickness: 3.5mm
- * Gasket and Nut are packed separately in PE bags.
(Gasket/Nut不組裝, 散裝出貨)



3 Pin 2 Pin
Pin Assignments Front View

UNIT : mm			TITLE			Amphenol LTW			ITEM NO		DRAWN BY		DATE										
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°			MINI PANEL SCREW M CONN M PIN			安費諾亮泰企業股份有限公司			AAD-XXPMMS-LC7001		Vicky		2019-03-04										
			SCALE	2:1	SIZE										A4	SHEET	1	OF	1				
			REV.	B	WC-REV.										A.3	QC: Inspection item							
			2			3			4			5			6			7			8		