





D

C

B

A




1. CODING IS AS FOLLOWS. SEE TABLE 1.
2. APPLIED RECEPTACLE CONTACT P/N:
- | DESCRIPTION | 2.8mm SENSOR-FLAT RECEPTACLE OR EQUIVALENT |
|-------------|--|
| PART NO. | 967542 OR EQU 967543 OR EQU |
| WIRE SIZE | 0.5~1.0 >1.0~2.5 |
3. APPLIED WIRE SEAL P/N:
- | DESCRIPTION | SINGLE-WIRE SEAL (5mm HOLE) |
|---------------------|-----------------------------|
| PART NO. | 828904 828905 |
| INSULATION DIA. (Ø) | 1.2~2.1mm 2.2~3.0mm |
4. LASERPRINT MARK THE PRODUCT PART NUMBER. CHARACTER SIZE APPROX 1.2MM RAISE. CHARACTER LOCATION AND ORIENTATION AS SHOWN
5. LASERPRINT MARK DATE CODE: IDENTIFIES THE YEAR, MONTH, DAY AND HOUR OF ASSEMBLY. YEAR: FIRST AND SECOND DIGITS (17=2017) MONTH: THIRD DIGIT, EXCLUDING 1, A=JAN, B=FEB, C=MARCH... (K=OCTOBER) DAY: FOURTH AND FIFTH DIGITS (14=14th DAY) HOUR: SIXTH AND SEVENTH DIGITS (11=11AM)
6. SUPPLY CONDITION: HINGE IN PRELOCKED POSITION
7. SUPPLY CONDITION: CPA IN PRELOCKED POSITION

TABLE 1

CODE 1: 2345390-1	CODE 11: 2345390-2
9.0	5.0

1	1	PC	RED	PA46-GF15	CPA	4
1	1	PC	GREEN	SILICON	INNER SEAL	3
1		PC	YELLOW	PA6-GF25	CODE 11	2
	1	PC	BLUE	PA6-GF25	CODE 1	2
1	1	PC	BLACK	PA6-GF25	HOUSING	1
-2	-1	U/M	COLOR	MATERIAL	DESCRIPTION	ITEM
B	B	REVISION OF EACH ASSY NO.				
5.6	5.6	WEIGHT OF EACH ASSY NO. [g]				
QTY PER ASSY		PARTS LIST				

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. ZHAO CHK E. JIANG APVD I. YIN		26APR2019 26APR2019 26APR2019		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3		NAME SEALED-3P-PLUG-CPA-ASSEMBLY (FLAT SENSOR CONNECTOR)		RESTRICTED TO	
		0 PLG ± 1 PLG ± 2 PLG ± 3 PLG ± 4 PLG ± ANGLES ±5° FINISH					
MATERIAL		WEIGHT					
SEE TABLE		N/A		A2		CAGE CODE C=2345390	
CUSTOMER DRAWING				SCALE 2:1		SHEET 1 OF 1	
						REV B	