


DESCRIPTION: MALE // D-SUB CRIMP CONTACT // LOOSE

SPECIFICATIONS:

MATERIALS:

CONTACT: BRASS  
PLATING: SEE P/N TABLE BELOW  
AMPERAGE: 5A MAX



| PART NUMBER     | PLATING                                                | WIRE AWG RANGE |
|-----------------|--------------------------------------------------------|----------------|
| 170-101-170L001 | GOLD FLASH ON MATING AREA // NICKEL ON WIRE CRIMP AREA | 20-28 AWG      |
| 170-101-170L002 | 10μ" GOLD OVER 50μ" NICKEL ENTIRE CONTACT              | 20-28 AWG      |
| 170-101-170L003 | 30μ" GOLD OVER 100μ" NICKEL ENTIRE CONTACT             | 20-28 AWG      |

NOTE: CONTACTS SUPPLIED IN BAGS OF 500/pcs

NORCOMP CRIMP TOOL PART NUMBER => 170-701-170-000

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:  
P. JENKINS

DATE:  
05/23/2002

UNITS = mm

DO NOT SCALE FROM DRAWING

NorComp

SCALE:  
NTS

SHEET 1 OF 1

REV 5

DWG NO. 170-101-170L00Y