

9001K11J1

Illuminated selector switch head, Harmony
9001K, metal, without handle, 30mm, 2
positions, stay put, 110-120V



Main

Product or Component Type	Head for illuminated selector switch
Device short name	K
Enclosure type	Dust and oil resistant weatherproof enclosure indoor/outdoor
Mounting diameter	1.18 in (30 mm)
Range of Product	Harmony 9001K

Complementary

Bezel material	Metal
Bulb base	BA 9s
Cap/operator or lens colour	Without cap
Contacts type and composition	Without contact block
Light block supply	Via transformer 120 V AC 50/60 Hz Via transformer 110 V AC 50/60 Hz
Operator position information	2 positions
Operator profile	Without handle
Operator profile	1 projecting push-button
Size	30 mm
Type of operator	Maintained
[Us] rated supply voltage	110...120 V
Light block supply	Via integral transformer
Type of operator	Stay put
Contacts type and composition	Without contact block

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03 CE

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	3389118043657
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.80 in (4.572 cm)
Package 1 Width	2.10 in (5.334 cm)
Package 1 Length	3.60 in (9.144 cm)
Package 1 Weight	9.60 oz (272.155 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------