









1	2	3	4	5	6	7	8
				REV. B	ECN NO. LE3-710137	DATE 2006/12/11	SIGN DongYaLi DESCRIPTION Change DOR0046SI70 To DOR00010016 And Move DOR00010016 To ZSE00100617
F							
E						Screw L=5.0 For Panel Thickness Under 1.2mm 適用板厚為1.2mm以下	
D						Screw L=6.0 For Panel Thickness Between 1.2~2.0mm 適用板厚為1.2~2.0mm	
C			Note: * @@ Important Dimension. * Waterproof Rate : IP68 IP68:1M of depth of water 24 hours (防水等級 IP68) (IP68:1米水深 24小時) * Do Mating Test After Glued 點膠後, 須作對插測試 * D-SUB Conn. : Black Core,PBT * Plastic Jacket : Black,Nylon+GF * Pin : Copper Alloy , Gold Plated * Ring : Light Blue,Silicone * Screw : Copper Alloy,Nickel Plated,#4-40 UNC				
B	 25 Pin Male Connector PCB Pin Layout					Recommended Panel Cut-Out 建議挖孔尺寸	
A	UNIT:mm TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°	TITLE D-SUB Conn. Panel Screw DB25P M Conn. M Pin SCALE Free SHEET 1 OF 1 REV. B SIZE A4 @@ :Inspection Item	Amphenol LTW 安費諾亮泰企業股份有限公司	ITEM NO SDB-25PMMP-SR8001 DWG NO SDB-25PMMP-SR8001 CUSTOMER ALTW	DRAWN BY DongYaLi CHECKED BY SIMON APPROVED BY MAX	DATE 2006/12/11 DATE 2006/12/22 DATE 2006/12/22	8 FMWIO702-01-01A2

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.