



LOC	DIST	P	F	REVISIONS			
				ZONE	LTR	DESCRIPTION	DATE
DF	BO				J	REV & REDRAWN DF-4297 PY	11-91
					K	REV PER 0600-4161-95 JB	08-30-95



- 1 MATERIAL: DIALLYL PHTHALATE PER MIL-M-14,TYPE SDG-F,COLOR:BLUE
- 2 MATERIAL: PHENOLIC PER MIL-M-14,TYPE CFG OR MFH,COLOR:BLACK
- 3 AMP PART NO,DATE CODE,CSA CERT,AND ARROWS MARKED WITH WHITE INK OR BY LASER MARKING AT APPROX AREA SHOWN,EITHER SIDE
4. THIS MODULE WILL ACCOMMODATE:
(23) SUBMINIATURE COAXICON,TYPE II SIZE 16,
TYPE III(+) SIZE 16 OR TYPE VI SIZE 16
SOCKET CONTACTS

OBSOLETE	202651-7
OBSOLETE	202651-6
2	202651-4
1	202651-2
MATERIAL	PART NUMBER

			PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES [mm] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± .005 ANGLES ± - MATERIAL SEE TABLE	DR 9-10-91 P.YEAGER	AMP AMP Incorporated Harrisburg, PA 17105-3608		
	CHK 11-12-91 D.B.MUMMEY			
	APPD 11-12-91 D.B.MUMMEY			
	APPD - -	NAME FEMALE BLOCK G SERIES,23 POSN		
	PRODUCT SPEC -			
FINISH -	APPLICATION SPEC -	SIZE C	CAGE CODE 00779	DRAWING NO 202651
	WEIGHT -	SCALE 4:1		SHEET 1 OF 1