






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED PER ECO-19-002122	11FEB2019	NLE	JWH



2289732-1 AS SHOWN

1 HOUSING - POLYESTER PBT, COLOR: SEE TABLE, GLASS FILLED
CPA - POLYESTER PBT, COLOR TRAFFIC RED, GLASS FILLED
SECONDARY LOCK - POLYESTER PBT, WATER BLUE, GLASS FILLED

2 CABLE ASSEMBLY: SEE TABLE.


3 FEMALE INTERFACE PER ISO-20860-1, ISO-20860-2, SAE/USCAR-17, SAE/USCAR-18.

4 SECONDARY LOCK AND CPA IN PRESET POSITION. IF SECONDARY LOCK IS IN FULLY LOCKED POSITION, SEE 408-162008 FOR INSTRUCTIONS TO RESET SECONDARY LOCK TO PRESET POSITION.


WITHOUT CPA	(SOLD SEPARATELY) SEE SHEET 2	Z	PER DETAIL Z	WATER BLUE	4-2289732-0
		N	PER DETAIL N	PASTEL GREEN	3-2289732-3
		M	PER DETAIL M	PASTEL ORANGE	3-2289732-2
		L	PER DETAIL L	CARMINE RED	3-2289732-1
		K	PER DETAIL K	CURRY	3-2289732-0
		I	PER DETAIL I	BEIGE	2-2289732-9
		H	PER DETAIL H	HEATHER VIOLET	2-2289732-8
		G	PER DETAIL G	BLUE GREY	2-2289732-7
		F	PER DETAIL F	NUT BROWN	2-2289732-6
		E	PER DETAIL E	LEAF GREEN	2-2289732-5
		D	PER DETAIL D	CLARET VIOLET	2-2289732-4
		C	PER DETAIL C	SIGNAL BLUE	2-2289732-3
		B	PER DETAIL B	CREAM	2-2289732-2
A		PER DETAIL A	JET BLACK	2-2289732-1	
WITH CPA		Z	PER DETAIL Z	WATER BLUE	2-2289732-0
		N	PER DETAIL N	PASTEL GREEN	1-2289732-3
		M	PER DETAIL M	PASTEL ORANGE	1-2289732-2
		L	PER DETAIL L	CARMINE RED	1-2289732-1
		K	PER DETAIL K	CURRY	1-2289732-0
		I	PER DETAIL I	BEIGE	2289732-9
		H	PER DETAIL H	HEATHER VIOLET	2289732-8
		G	PER DETAIL G	BLUE GREY	2289732-7
		F	PER DETAIL F	NUT BROWN	2289732-6
		E	PER DETAIL E	LEAF GREEN	2289732-5
		D	PER DETAIL D	CLARET VIOLET	2289732-4
		C	PER DETAIL C	SIGNAL BLUE	2289732-3
		B	PER DETAIL B	CREAM	2289732-2
		A	PER DETAIL A	JET BLACK	2289732-1
	COMMENTS	CABLE ASSEMBLY QTY=2	CODING REF	KEYING	CODING COLOR

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.J.HARDY CHK D.J.LANE APVD D.J.LANE	14APR2015 14APR2015 14APR2015	TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		PRODUCT SPEC 108-32137 APPLICATION SPEC 114-32145	
MATERIAL		WEIGHT		SIZE CAGE CODE DRAWING NO	
1		-		A1 - C=2289732	
CUSTOMER DRAWING		RESTRICTED TO		SCALE 6:1 SHEET 1 OF 2 REV A	


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




2289732-1 AS SHOWN
SCALE 4:1




DETAIL A
SCALE 3:1




DETAIL B
SCALE 3:1




DETAIL C
SCALE 3:1




DETAIL D
SCALE 3:1




DETAIL E
SCALE 3:1




DETAIL F
SCALE 3:1




DETAIL G
SCALE 3:1




DETAIL H
SCALE 3:1




DETAIL I
SCALE 3:1




DETAIL K
SCALE 3:1




DETAIL L
SCALE 3:1



DETAIL M
SCALE 3:1



DETAIL N
SCALE 3:1



DETAIL Z
SCALE 3:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.J.HARDY 14APR2015	 TE Connectivity	
DIMENSIONS:		CHK D.J.LANE 14APR2015		
mm		APVD D.J.LANE 14APR2015		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		
0 PLC ±		108-32137	NAME FEMALE KIT, CPA, CLIP SLOT, 2 POSITION, FAKRA AUTOMATED	
1 PLC ±		APPLICATION SPEC		
2 PLC ±		114-32145	SIZE A1	
3 PLC ±		WEIGHT	CAGE CODE -	
4 PLC ±		CUSTOMER DRAWING	DRAWING NO C=2289732	
ANGLES ±		SCALE 6:1	SHEET 2 OF 2	
FINISH		REV A		