



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		D	REVISED ECO-05-007228	30AUG2005	SW	CR
			DI	ADDED 1--5, ECO-05-010011	09NOV2005	SW	CR
			E	REVISED ECO-06-022418	26SEP2006	SW	CR
			F	REVISED PER ECO-08-003247	06FEB2008	SS	CR

D



C

B


A



- 1 MATERIAL AND FINISH
HOUSING: PA 6.6, UL 94 V-0 RATED, COLOR: GREEN.
CLAMP: BRASS, NICKEL PLATED.
TERMINAL: BRASS, TIN PLATED.
CONTACT SPRING: PHOSPHOR BRONZE, TIN PLATED.
CLAMPING SCREW: BRASS, NICKEL PLATED.
2. END-TO-END STACKABLE WITHOUT LOSS OF CENTERLINE SPACING.
3. WIRE RANGE: 14-30 AWG.
- 4 NOT CUMULATIVE TOLERANCE.
5. BUCHANAN LOGO TO APPEAR ON HOUSING, LOCATION OPTIONAL WHERE SPACE PERMITS.
- 6 MARKED WITH PERMANENT WHITE INK IN APPROX AREA SHOWN.




1546173-3 AS SHOWN



DETAIL Z

PRELIMINARY	SEE DETAIL Z	4	ALL	20.0	4	1-1546173-5
	-	5	1, 3, 5, 7, 8	40.0	8	1-1546173-4
	-	12	ALL	60.0	12	1-1546173-2
	-	11	ALL	55.0	11	1-1546173-1
	-	10	ALL	50.0	10	1-1546173-0
	-	9	ALL	45.0	9	1546173-9
	-	8	ALL	40.0	8	1546173-8
	-	7	ALL	35.0	7	1546173-7
	-	6	ALL	30.0	6	1546173-6
	-	5	ALL	25.0	5	1546173-5
SPECIAL MARKING	-	4	ALL	20.0	4	1546173-4
	-	3	ALL	15.0	3	1546173-3
	-	2	ALL	10.0	2	1546173-2
	QTY	SELECTIVELY LOADED IN POSTIONS		L	NO OF POSN	PART NUMBER
	CONTACTS					

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.			DWN S. WELDON 18APR2002	Tyco Electronics Harrisburg, PA 17105-3608		
DIMENSIONS: mm			CHK D. BIEVENOUR 18APR2002	NAME TERMINAL BLOCK, PLUG, 90 DEGREE, STACKING, 5.0mm PITCH		
TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD D. BIEVENOUR 18APR2002			
			PRODUCT SPEC -			
0 PLC ± 1 PLC ±0.3 2 PLC ±0.25 3 PLC ±0.000 4 PLC ±0.0000			APPLICATION SPEC -	SIZE	CAGE CODE	DRAWING NO
MATERIAL 			WEIGHT -	A200779		C-1546173
FINISH -			CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1
					REV F	