

Han EMC/B 10 Hood side entry M32



Image is for illustration purposes only. Please refer to product description.

Part number	19 62 810 0547
Specification	Han EMC/B 10 Hood side entry M32
HARTING eCatalogue	https://b2b.harting.com/19628100547

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] EMC/B
Type of hood/housing	Hood
Type	High construction

Version

Size	10 B
Version	Side entry
Cable entry	1x M32
Locking type	Single locking lever
Field of application	Hoods/Housings for higher EMC requirements

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 IP66
Type rating acc. to UL 50 / UL 50E	4 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted



Pushing Performance
Since 1945

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE
	DNV GL

Commercial data

Packaging size	1
Net weight	158 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140132771
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors