

Han-Eco Mod.16 flange gasket-HBM



Image is for illustration purposes only. Please refer to product description.

Part number	19 41 000 9803
Specification	Han-Eco Mod.16 flange gasket-HBM
HARTING eCatalogue	https://b2b.harting.com/19410009803

Identification

Category	Accessories
Series of hoods/housings	Han-Eco® Modular
Type of accessory	Flange gasket

Version

Size	16 B
------	------

Material properties

Material (seal)	NBR
Colour (seal)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)



Pushing Performance
Since 1945

Commercial data

Packaging size	10
Net weight	9.5 g
Country of origin	Germany
European customs tariff number	40169300
GTIN	5713140130609
ETIM	EC002943
eCl@ss	27440291 Connector component (parts)