

LOC B	DIST -	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			H	ECR-11-018847	13/09/11	JB	MG
			J	ECR-11-023742	22/11/11	JB	MG

D

D

C


C

B




B

A



A



SEE DETAIL A




NOTE
BOWING: AFTER UPPER TIE BAR REMOVAL-1.5mm MAX. FOR 500mm
PITCH: AFTER UPPER TIE BAR REMOVAL-2.54±0.127
INTERIOR RADS 0.1mm TYPICAL



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL
SEE ABOVE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±0.05
3 PLC ±
4 PLC ±
ANGLES ±0.5
FINISH -

DWN J.BRIGHT 19/08/11

CHK M.GREENER 19/08/11

APVD D.PENNINGTON 19/08/11

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

2	Ni & Sn	0-1544179-4
2	Sn	0-1544179-3
1	Ni & Sn	0-1544179-2
1	Sn	0-1544179-1
REELING	FINISH	PART NUMBER



TE Connectivity

NAME
DIL CONTACT
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-1544179	-

SCALE NTS
SHEET 1 OF 1
REV J