



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	19APR2019	SS	KMA
	B	ECR-19-018070	18NOV2019	SS	JK



2355444-1 AS SHOWN

Notes:

1. Material and Finish:

- Protective Cover: Zinc Die-Cast, Nickel Plated
- Cover Gasket: Silicon, Color: Transparent
- Ball Chain Assembly: Copper Alloy and Stainless steel, Nickel Plated

2. Operating Temperature: -40°C to +85°C

3. IP67 rated when fully mated with the appropriate connector

4. RoHS compliant

5. Packaging Spec: 107-19763

6. Material and Finish:



- Protective Cover: PBT UL 94 V-0, black
- Cover Gasket: Silicon, Color: Transparent
- Tether: PE black

E81956	6	2355444-2
E81956	1	2355444-1
UL NO.	MATERIAL	TEPN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.SHARMA CHK K.MALCZYK APVD J.de BRUIJN	19APR2019 24APR2019 24APR2019	NAME TE Connectivity
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.50 1 PLC ± 0.38 2 PLC ± 0.25 3 PLC ± 0.10 4 PLC ± 0.05 ANGLES $\pm 3^\circ$			
		PRODUCT SPEC	-	PROTECTIVE COVER ASSEMBLY KIT
	APPLICATION SPEC 114-19162		-	
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT -	SIZE A3	CAGE CODE 00779
			DRAWING NO C-2355444	RESTRICTED TO -
			CUSTOMER DRAWING	SCALE 1:1
				SHEET 1 OF 2
				REV B

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-		SEE SHEET 1	-	-	-



2355444-2 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0	PLC	± 0.50
1	PLC	± 0.38
2	PLC	± 0.25
3	PLC	± 0.10
4	PLC ANGLES	$\pm 3^\circ$

MATERIAL

SEE TABLE

FINISH

SEE TABLE

DWN 19APR2019
S.SHARMACHK 24APR2019
K.MALCZYKAPVD 24APR2019
J.de BRUIJN

PRODUCT SPEC

APPLICATION SPEC

114-19162

WEIGHT -



TE Connectivity

PROTECTIVE COVER ASSEMBLY KIT

-

-

NAME

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C-2355444 -

CUSTOMER DRAWING SCALE 1:1 SHEET 2 OF 2 REV B