

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD

E

REV PER 063A-0541-00

25SEP00

JR

TM

1

WIRE INSULATION DIA IS 1.65-1.88
[.065-.074].

RING "A"
COLOR: VIOLET

RING "B"
COLOR: GREEN

SLEEVE

3.05
[.120]

7.87
[.310]

2.54
[.100]
REF 2 PLC

13.34
[.525] MAX

TEFLON ASTM D-1710

SLEEVE

COPPER PER ASTM B152 / NICKEL PL PER QQ-N-290

RING "B"

COPPER PER ASTM B152 / NICKEL PL PER QQ-N-290

RING "A"

MATERIAL / FINISH

DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
JR RUTH
31MAY00

CHK
R HERSEY
31MAY00

APVD
T MICHIELUTTI
31MAY00

NAME

AMP Incorporated
Harrisburg, PA 17105-3608

DIMENSIONS:
MM [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±-
2 PLC ±0.40[.015]
3 PLC ±-
4 PLC ±-
ANGLES ±-

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
—

MATERIAL
SEE TABLE

FINISH
SEE TABLE

CUSTOMER DRAWING

PRE-INSULATED SPARE WIRE CAP

SIZE
A3

CAGE CODE
00779

DRAWING NO
C- 328858

RESTRICTED TO
—

SCALE
10:1

SHEET
1 OF 1

REV
E

AMP 1470-19 REV 11JUN97

25-SEP-00 13:53:23 amp13469 /home/amp13469/ednmod