






RECOMMENDED PANEL MOUNTING



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. ELECTRICAL LIFE: 50,000 OPERATIONS
5. INSULATION RESISTANCE: 1,000 M Ω MIN.
6. OPERATING TEMP.: -25°C to 70°C (No Lamp)
- ▲ 7. LAMP VOLTAGE: N/A
8. ▲ DENOTES CRITICAL PARAMETER.
9. RATING: 5A @ 250 VAC, 8A @ 125VAC
6A @ 24 VDC
10. SEAL RATING: IP40
- ▲ 11. TRAVEL: 3.0mm FULL - MOMENTARY

PARTS LIST			
ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	F040004	D16EET11 HOUSING
2	1	F050206	50-002-06 ACTUATOR - WHITE TRANSPARENT RECTANGULAR CONCAVED LENS
-	-	-	NO LAMP



TITLE D16OAT110WHT

A	24038	RELEASE	9/18/19	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 3:2	DATE 9/18/2019	DR MW	DWG XF0926P	REV A
--------------	-------------------	----------	----------------	----------