

4






3

2

1



THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		20
©	COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	05DEC2016	BH	BW
	A1	REVISED PER ECR-19-016175	18OCT2019	M.G	D.Z
	A2	REVISED PER ECR-20-007446	15JUN2020	M.G	D.Z



- NOTES.
- 1.GENERAL TOLERANCE : ± 0.3
 - 2.APPLICABLE CONTACT PART NUMBERS :
1743728-1, 1743729-1
1-2232902-2, 1-2232901-2
 - 3.APPLICABLE TPA P/N : 2108963-1

COPPER ALLOY	-	POST CONTACT	I	2108960-1
PA66	NATURAL	DISTRIBUTION HSG	I	
MATERIAL	COLOR	DESCRIPTION	Q'TY	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BH	06DEC2016		 TE Connectivity					
DIMENSIONS:		CHK -	-		NAME DISTRIBUTION CONNECTOR					
mm		APVD BW	-							
		PRODUCT SPEC 108-61268								
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-61016		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		WEIGHT -		A3		-	C-2108960	-
		MATERIAL		FINISH -		CUSTOMER DRAWING		SCALE		SHEET
SEE TABLE						2:1		1	1	A2