




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APV
	C 1	ECR-20-004642	13 OCT 2020	RK	SBH

Notes

- 1 SUITABLE HOUSINGS: SERIES EMV, SIZE 1
CUSTOMER DRAWING 1102700, 1106402, 1106200
- 2 STANDARDS:
DIN EN 61984, DIN EN 60664-1
- 3 SUR TEC 650 CHROMIT AL TCP PASSIVATION
- 4 PN 0-3 AND 0-1 WITHOUT PROFILE SEAL
- 5 TOOL:
PHILLIPS SCREWDRIVER PH1.
- 6 VARNISH ON INSIDE AREA NOT NECESSARY
- 7 PACKAGING:
10 SETS IN A CARTON.

	0-1102701-1	EMV-K.3/4.SG.1.13.G
OBSOLETE	0-1102701-3	EMV-K.3/4.SG.1.11.G-S0
	4-1102701-5	EMV-K.3/4.SG.1.11.G
OBSOLETE	3-1102701-5	EMV.3/4.SG.1.11.G
	PART NO.	ORDERING TEXT



PN 3-5 AS SHOWN

								PART NO.	ORDERING TEXT
1	1	1	1	SCREW COUNTERSUNK RAISED HEAD		STAINL. STEEL V2A	-	M3x8 PH1 DIN EN ISO 7047	7
1	1	1	1	O - RING		NBR	BLACK	3.0x1.0	6
-	-	1	1	PROFILE SEAL		FKM	BLACK	SERIES EMV / HIP	5
1	-	-	-	ANGLED BULKHEAD HOUSING	PG13	ALU	BLACK SEE NOTE 	SERIES EMV-K	4
-	1	1	-	ANGLED BULKHEAD HOUSING	PG11	ALU	BLACK SEE NOTE 	SERIES EMV-K	2
-	-	-	1	ANGLED BULKHEAD HOUSING	PG11	ALU	GREY	SERIES EMV	1
0-1	0-3	4-5	3-5	DESCRIPTION	"A"	MATERIAL	COLOR/SURFACE	NOTE	ITEM NO.
PN/QTY									
PARTS LIST (PER ONE UNIT)									

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN V. GLUMM		26AUG2009		 TE Connectivity									
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK H. Braun		26AUG2009		NAME							
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±1°		APVD T. Schnurpfeil		26AUG2009		ANGLED BULKHEAD HOUSING ASS'Y SIDE ENTRY, SERIES EMV, SIZE 1							
				PRODUCT SPEC		-		-							
				APPLICATION SPEC		-		-		-					
MATERIAL -		FINISH -		WEIGHT -		SIZE A 3		CAGE CODE 00779		DRAWING NO C=1102701		RESTRICTED TO -			
CUSTOMER DRAWING										SCALE 1:1		SHEET 1 OF 1		REV C 1	