








RECOMMENDED PCB LAYOUT
FOR USE WITH 0.20 [.008] THICK STENCIL

6	7	56mm	35.56 [1.400]	14	37.69 [1.484]	30	6-147292-4
6	7	44mm	30.48 [1.200]	12	32.61 [1.284]	26	6-147292-3
6	7	32mm	17.78 [.700]	7	19.91 [.784]	16	6-147292-2
6	7	24mm	12.70 [.500]	5	14.83 [.584]	12	6-147292-1
	7	56mm	33.02 [1.300]	13	35.15 [1.384]	28	6-147292-0
	7	44mm	25.14 [.900]	9	24.99 [.984]	20	5-147292-9
6	7	44mm	25.4 [1.000]	10	27.53 [1.084]	22	5-147292-8
6	7	44mm	27.94 [1.100]	11	30.07 [1.184]	24	5-147292-7
	7	24mm	7.62 [.300]	3	9.75 [.384]	8	5-147292-6
	7	32mm	20.32 [.800]	8	22.45 [.884]	18	5-147292-5
6	7	24mm	5.08 [.200]	2	72.14 [.284]	6	5-147292-4
	7	24mm	2.54 [.100]	1	4.67 [.184]	4	5-147292-3
	7	24mm	10.16 [.400]	4	12.29 [.484]	10	5-147292-2
6	7	32mm	15.24 [.600]	6	17.37 [.684]	14	5-147292-1
	3	56mm	35.56 [1.400]	14	37.69 [1.484]	30	147292-8
	3	44mm	27.94 [1.100]	11	30.07 [1.184]	24	147292-7
9	3	24mm	7.62 [.300]	3	9.75 [.384]	8	147292-6
9	3	32mm	17.78 [.700]	7	19.91 [.784]	16	147292-5
9	3	24mm	5.08 [.200]	2	72.14 [.284]	6	147292-4
9	3	24mm	2.54 [.100]	1	4.67 [.184]	4	147292-3
9	3	24mm	10.16 [.400]	4	12.29 [.484]	10	147292-2
8	3	32mm	15.24 [.600]	6	17.37 [.684]	14	147292-1
PLATING		TAPE WIDTH	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN B. HAYMAKER		27MAR99		 TE Connectivity			TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD J.GESFORD		27MAR99		NAME			SURFACE MOUNT HDR ASSY, MOD II, B/A, VERT, D/R, .100 X.100 C/L, .025 SQ POST,						RESTRICTED TO	
DIMENSIONS: mm [INCHES]						0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13[.005] 4 PLC ± - ANGLES ± -				PRODUCT SPEC —			APPLICATION SPEC —			SIZE A2		CAGE CODE —		DRAWING NO C-147292			SCALE 4:1		SHEET 1 OF 1		REV M
MATERIAL 						FINISH SEE TABLE			WEIGHT —			CUSTOMER DRAWING															