

5

4

3




2

1

SPECIFICATION

Mating Cycles	500
Filter type	C
Capacitance	3900pf±20%
Working Voltage	100v
Current Rating	7.5A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION (dB)
5	6dB
10	11dB
50	25dB
100	35dB
500	35dB
1000	32dB



				Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, Female, Straight 25 Poles, solder buckets, tin plated shell with clinch nuts	Maßstab/ Scale 1.5:1
			Detail.	8-JUL-02	CV			
			Insp.					
			Stand.					
33271	28/11/05	JMDR						
32236	13/10/04	TR						
31058	8-JUL-02	CV						
Mod.	Dat.	Name						
			HARTING EURL F-95972 Paris				TB 0964311724x	Blatt / Page 1 / 1
							Sub.	

09643117248	M3
09643117247	UNC 4-40
Part number	Nut thread