

VGM32-SS68 15-25 BG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	Heavy-duty connectors, Accessories, Cable glands, Stainless steel 1.4305 (303)
Order No.	1193580000
Type	VGM32-SS68 15-25 BG
GTIN (EAN)	4032248976553
Qty.	25 pc(s).

VGM32-SS68 15-25 BG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Length	40 mm	Length (inches)	1.575 inch
Net weight	101 g		

Temperatures

Limit temperature	-40 °C ... 130 °C
-------------------	-------------------

General information

AF size	36 mm	Cable glands	M 32
External thread	M 32	Length of thread	8 mm
Material	Stainless steel 1.4305 (303)	O-Ring	Silicone
Protection degree	IP68 - 15 bar	Standards	EN 45545-2:2013
UL 94 flammability rating	V-0		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-32	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32	ECLASS 12.0	27-14-08-01

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN