

Han PushPull SCRJ metal PFT



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 242 0313
Specification	Han PushPull SCRJ metal PFT
HARTING eCatalogue	https://b2b.harting.com/09352420313

Identification

Category	Connectors
Series	Han® PushPull (V14)
Identification	SCRJ
Element	Panel feed through
Specification	AIDA compliant
Type of contact	SC contact
Features	Intuitive locking mechanism

Version

Shielding	Unshielded
Number of contacts	2
Locking type	PushPull
Pack contents	Without contacts

Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated



Pushing Performance
Since 1945

Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
	Naphthalene

Specifications and approvals

Specifications	IEC 61076-3-117 Variant 14 (V14)
	IEC 61754-24 Mating face
UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	28.46 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140054431
ETIM	EC002636
eCl@ss	27440114 Rectangular connector (for field assembly)