




JKL LAMP NUMBER	VOLTS RATED	AMPS $\pm 10\%$	*MSCP $\pm 25\%$	*LUMENS $\pm 25\%$	AVERAGE LIFE HRS.	FILAMENT TYPE
6ESB	6.0	.040	.024	0.30	10,000	C-6V
10ESB	10.0	.040	.048	0.60	10,000	C-2V
12ESB	12.0	.040	.088	1.11	7,500	C-2F
24ESB	24.0	.040	.120	1.51	8,000	C-2F
28ESB	28.0	.040	.287	3.61	6,000	C-2F
48ESB	48.0	.040	.358	4.50	5,000	CC-2F

			METRIC THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0		JKL COMPONENTS CORPORATION			
			DRAWN BY L. WENGSTROM		APPV'D BY QC		DATE 8/16/00		TITLE T-2 TELEPHONE SLIDE BASE ANSI #5-23mol	
RELEASED			8/16/00		SIZE A		FSCM NO. 55335		DRAWING NO. SLIDE BASE ANSI #5-23mol	
REV. NO.			DESCRIPTION/ECO NUMBER		APPV'D DATE		- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE NONE	
					RELEASED DATE 8/16/00		REVISION DATE		REV. NO. SHEET 1 OF 1	