





LOC	DIST	REVISIONS					
DF	DO	P	LTR	DESCRIPTION	DATE	DWN	APVD
			0	PRPOPSAL DRAWING	4-01	CT	DM



VIEW Z-Z
SHOWN WITHOUT
CONTACTS & STANDOFFS



RECOMMENDED P.C. BOARD LAYOUT
SHELL SIZE 5 (50 POSITION)

.230 [5.84] .220 [5.59]	.033 [0.84] .027 [0.69]	.171 [4.34] .131 [3.33]	.040 [1.02] .020 [0.51]	.544 [13.82] .524 [13.31]	2.188 [55.58] 2.168 [55.07]	.248 [6.30] .238 [6.05]	.439 [11.15] .419 [10.64]	.620 [15.75] .590 [14.99]	.428 [10.87] .418 [10.62]	2.411 [61.24] 2.401 [60.99]	2.069 [52.55] 2.059 [52.30]	2.650 [67.31] 2.620 [66.55]	M518277-1	50	5	1218997-5
P	N	M	L	J	H	G	F	E	D	C	B	A	INSERT ARRANGEMENT	NO OF POS	SHELL SIZE	PART NUMBER

PRELIMINARY- NOT RELEASED FOR PRODUCTION

THIS DRAWING IS A CONTROLLED DOCUMENT.									
DIMENSIONS, (INCHES) (mm)		DWG D. C. THOMAS 4-23-01		 AMP Incorporated Harrisburg, PA 17105-3608					
		CIR D. MILLER 4-23-01							
 D .001 P L/C ±.001 P L/C ±.001 P L/C ±.001 R P L/C ±.001 ANGLES ±.001		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME AMPLIMITE RECEPTACLE ASSY, LOW PROFILE SIZE 20 POSTED P.C. BOARD CONTACTS SERIES 109, SIZE 5					
		PRODUCT SPEC — APPLICATION SPEC							
MATERIAL	FINISH	WEIGHT —		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
SEE CALLOUTS	SEE CALLOUTS			A1	00779	C- 1218997	—		
CUSTOMER DRAWING				SCALE	1 OF 1 SHEET REV 0				