

Han B Protect Cover Die Cast (Easy hood)



Image is for illustration purposes only. Please refer to product description.

Part number	11 30 016 5422
Specification	Han B Protect Cover Die Cast (Easy hood)
HARTING eCatalogue	https://b2b.harting.com/11300165422

Identification

Category	Accessories
Series of hoods/housings	Han [®] Easy Hood
Type of accessory	Protection cover
Description of the accessory	for hoods Metal With fixing cord

Version

Size	16 B
Locking type	Double locking lever
Han-Easy Lock [®]	Yes

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP54
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (seal)	NBR
Material (locking)	Polycarbonate (PC) Stainless steel
Colour (locking)	RAL 7037 (dust grey)
RoHS	compliant



Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
ECHA SCIP number	60b1a572-bb3f-476f-9307-b7d1688bd90c
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
	Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	102 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140110823
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors