






D


C

B


A

POLARIZATION TYPES



POLARIZATION TYPE "A"	POLARIZATION TYPE "B"	POLARIZATION TYPE "C"
		
PN: 2213263-1	PN: 2213263-2	PN: 2213263-3
POLARIZATION TYPE "D"	POLARIZATION TYPE "E"	
		
PN: 2213263-4	PN: 2213263-5	




3D VIEWS
FOR REFERENCE ONLY



1.5 - 4.0
RECOMMENDED
PANEL
THICKNESS



RECOMMENDED
PANEL CUTOUT
SCALE 5:2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SHAFFER 12NOV2013	 TE Connectivity					
DIMENSIONS: mm		CHK M. LUKSIC 12NOV2013						
		APVD M. LUKSIC 12NOV2013	NAME PANEL MOUNT, SOCKET; SEALED NECTOR M, 7 POLE -					
		PRODUCT SPEC 108-133014						
		APPLICATION SPEC 114-32111						
		WEIGHT -						
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.2 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ± FINISH			SIZE A2	CAGE CODE -	DRAWING NO C=2213263	RESTRICTED TO -		
MATERIAL NOTE 1			SCALE 2:1				SHEET 2 OF 2	REV B1
		CUSTOMER DRAWING						