

## Pneumatic contact male 3,0 mm



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Contacts
Type of contact	Pneumatic contact
Description of the contact	Without shut-off Straight

### Version

Gender	Male
Manufacturing process	Turned contacts

### Technical characteristics

Limiting temperature	-40 ... +80 °C
Operating pressure	≤8 bar
Tube inner diameter	3 mm

### Material properties

Material (contacts)	Delrin acetal
Material (seal)	Buna-N
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No

## Material properties

REACH SVHC substances	No
-----------------------	----

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

## Commercial data

Packaging size	10
Net weight	0.754 g
Country of origin	Germany
European customs tariff number	39269097
eCl@ss	27440204 Contact for industrial connectors