

Sealing cap - PROT-M 8 FS-PA-CHAIN-EYE - 1441082

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



M8 sealing cap made of plastic with fixing band, for free M8 connectors, with 7.5 mm fastening eye

RoHS

Key Commercial Data

Packing unit	10 pc
GTIN	 4 046356 501484
GTIN	4046356501484

Technical data

Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C
Degree of protection	IP65
	IP67

Material

Flammability rating according to UL 94	V0
Material	PA 6.6 GF
Sealing material	NBR
Additional material specifications	PUR (Holding band)

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Sealing cap - PROT-M 8 FS-PA-CHAIN-EYE - 1441082

Classifications

eCl@ss

eCl@ss 4.0	27140800
eCl@ss 4.1	27140800
eCl@ss 5.0	27143400
eCl@ss 5.1	27143400
eCl@ss 6.0	27379200
eCl@ss 7.0	27379218
eCl@ss 8.0	27379218
eCl@ss 9.0	27379218

ETIM

ETIM 3.0	EC000032
ETIM 4.0	EC002040
ETIM 5.0	EC002040
ETIM 6.0	EC002040
ETIM 7.0	EC002040

UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>