



APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/27/18	



PIN	BRASS
2:1	GOLD PLATED
A	BRASS
2:1	

SPECIFICATIONS:

Material:
 Insulator: PA66+30%GF, rated UL 94V-0
 Insulator color: Black
 Contacts: Brass
 Plating:
 Gold flash over Nickel underplate overall
 Electrical:
 Current rating: 7 Amp
 Contact resistance: 20 mohms max
 Insulation resistance: 1,000 Mohms min
 Dielectric withstanding voltage: 500 VAC
 Temperature Rating:
 -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS TOLERANCES: EXCEPT AS NOTED MM ANGLE X.X ± 0.30 ± 3' X.XX ± 0.25 X.XXX ± 0.10			ADAM TECH INTERCONNECTS 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS		DATE	TITLE	
DRAWN	AY	11/27/18	8+23P, AUTOMOBILE, PITCH 4.00, L1.3*17.5 PIN	
CHECKED	AC	11/27/18	SIZE X	PART NO. ADT-AMMC3903MACT002
APPROVED			REF: S00111C	SCALE: NTS
			SHEET 1	OF 1