





NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = 0.4
X.XX = 0.25
3. TERMINAL NUMBERS FOR REF. ONLY
4. CONTACT RATING: 5A @ 250V AC
8A @ 125V AC
6A @ 24V DC
5. CONTACT RESISTANCE: 100mΩ MAX. @ 2-4 VDC
6. ELECTRICAL LIFE: 50,000 CYCLES
7. TRAVEL: 3.0mm
8. CONTACT MATERIAL: COPPER ALLOY WITH SILVER PLATING
9. OPERATING TEMPERATURE: -25°C TO 55°C WITH LAMP
- ▲ 10. LAMP VOLTAGE: 6V DC YELLOW LED
11. DEGREE OF PROTECTION: IP 40
12. ▲ DENOTES CRITICAL PARAMETER
13. 2002/95/EC (ROHS) COMPLIANT

▲ Parts List

ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	F040013	P16EET11
2	1	F050206	50-002-06 (YELLOW LENS TRANSPARENT)
3	1	F051601	P16 TERMINAL PROTECTOR
4	1	F050418	50-004-18 6V DC LED (YELLOW)



TITLE P16EET11HYELYEL

A	21892	RELEASE FOR PRODUCTION	6/29/15	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE	DATE	DR	DWG	REV
1.5:1	6/29/2015	MW	XF0901P	A