





-
- Technical drawing of a component with the following dimensions and specifications:
- Dimensions:**
 - $H \pm .015$ [± 0.38]
 - $L \pm .010$ [± 0.25]
 - $J \pm .010$ [± 0.25]
 - $.050 \pm .020$ [1.27 ± 0.51] TYP
 - $.125$ [3.17] REF
 - Material Specifications:**
 - SHELL, FRONT & REAR
MAT'L: STEEL PER ASTM A 109
OR EQUIVALENT
FINISH: CADMIUM .00300-.000600 THK PER QQ-P-416
OVER COPPER .000050 MIN THK PER AMS 2148
 - GROMMET
MAT'L: SILICON RUBBER PER A-A-59588
COLOR: RED



THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: C.C.THOMAS 10-14-14	 TE Connectivity	
DIMENSIONS:		CHK: C.DERRICK 10-14-14	NAME: PLUG ASSY, SIZE 1-6, IP67 SERIES 90, AMPLITUDE WITH IF SEAL AND GROMMET	
TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APPD: C.DERRICK 10-14-14		
INCHES	0 PLC ± . 1 PLC ± . 2 PLC ± . 3 PLC ± .005 [0.13] 4 PLC ± . ANGLES ± 1°	PRODUCT SPEC	SIZE: A1 CASE CODE: 00779 DRAWING NO: 2221860 RESTRICTED TO: -	
	FINISH	APPLICATION SPEC		
MATERIAL: SEE CALLOUTS	SEE CALLOUTS	WEIGHT: 0.000000	CUSTOMER DRAWING	
		SCALE: 4:1	SHEET: 1 OF 1	REV: D