



## Main

Range of product	Harmony XD2
Product or Component Type	Complete joystick controller
Device short name	XD2
Mounting diameter	1.18 in (30 mm)
Bezel material	Chromium plated metal

## Complementary

Operator position information	All positions
Notch per direction	1
Operator direction information	2 directions
Contacts type and composition	1 C/O snap action
Short-circuit protection	10 A gG (gl) Neozed cartridge fuse EN/IEC 60947-5-1
Connections - terminals	Captive screw clamp terminals, 2 x 1.5 mm <sup>2</sup> with or without cable end Captive screw clamp terminals, 1 x 2.5 mm <sup>2</sup> with or without cable end
Electrical durability	1000000 Cycles, AC-15 230 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C 1000000 Cycles, AC-15 127 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C 1000000 Cycles, DC-13 24 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C 1000000 Cycles, DC-13 48 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C 1000000 Cycles, DC-13 120 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C 1000000 cycles, AC-15 48 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C
Contact code designation	A600-Q600
Overvoltage category	Class I IEC 61140
Mechanical durability	1000000 cycles
Fixing center	60 x 100 mm
Return	To 0 position
Height	4.37 in (111 mm)
Depth	2.68 in (68 mm)
Product Weight	0.49 lb(US) (0.22 kg)

## Environment

Standards	EN/IEC 60947-5-1
Product Certifications	CSA
Protective treatment	TC
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Vibration resistance	25 gn 10...500 Hz)IEC 60068-2-6
Shock resistance	50 gn IEC 60068-2-27
IP degree of protection	IP40 IEC 60529

## Ordering and shipping details

Category	22476 - JOYSTICKS (NOT CRANE)
Discount Schedule	I
GTIN	3389110348668
Nbr. of units in pkg.	1
Package weight(Lbs)	8.61 oz (244 g)
Returnability	No
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.36 in (6 cm)
Package 1 width	4.72 in (12 cm)
Package 1 Length	2.76 in (7 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	44
Package 2 Weight	24.64 lb(US) (11.176 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------