




D




- △ HOUSING: PBT, UL94V-0, COLOR BLUE.
POSTS: PHOSPHOR BRONZE.
- △ POSTS: 0.00076[.000030] MIN GOLD ON MATING AREA,
0.00254[.000100] MIN TIN ON SOLDER END, ALL OVER
0.00127[.000050] MIN NICKEL ON ENTIRE POST.
- △ TIN DATUMS S & T TO BE ESTABLISHED BY CUSTOMER.

C



SECTION U-U

B



RECOMMENDED PC BOARD LAYOUT
(VIEWED FROM CONNECTOR SIDE)

OBSOLETE	78.74 [3.100]	31	86.36 [3.400]	100.33 [3.950]	64	1-1761693-7
	73.66 [2.900]	29	81.28 [3.200]	95.25 [3.750]	60	1-1761693-6
OBSOLETE	48.26 [1.900]	19	55.88 [2.200]	69.85 [2.750]	40	1-1761693-3
	40.64 [1.600]	16	48.26 [1.900]	62.23 [2.450]	34	1-1761693-1
	27.94 [1.100]	11	35.56 [1.400]	49.53 [1.950]	24	1761693-8
OBSOLETE	22.86 [.900]	9	30.48 [1.200]	44.45 [1.750]	20	1761693-7
OBSOLETE	17.78 [.700]	7	25.40 [1.000]	39.37 [1.550]	16	1761693-6
OBSOLETE	15.24 [.600]	6	22.86 [.900]	36.83 [1.450]	14	1761693-5
	10.16 [.400]	4	17.78 [.700]	31.75 [1.250]	10	1761693-3
	D	C	B	A	NO OF POS	PART NUMBER

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. CRISAMORE/DJI CHK S. BOLASH APVD M. WALMSLEY	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± .01 1. PLC ± .01 2. PLC ± .01 3. PLC ± .01 4. PLC ± .01 ANGLES ± .01	OSJUNOS OSJUNOS OSJUNOS OSJUNOS OSJUNOS OSJUNOS	NAME	HEADLINE ASSEMBLY, VERTICAL, LOW PROFILE, IDC
MATERIAL	FINISH	WEIGHT	SIZE	RESTRICTED TO
△	△	—	A1 00779	—
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1	REV B