


Duplex Multimode Fiber Coupler (SC/ST)

MODEL NUMBER: N456-000



Highlights

- Dual SC/ST coupler for mating disparate cables
- High precision mating structure with low insertion loss
- Duplex adapter accepts two simplex connectors or one duplex connector

System Requirements

- Two cables with SC and ST fiber optic connectors

Package Includes

- Duplex SC to ST fiber optic coupler

Description

This coupler provides a simple and easy way to link together two fiber optic cables with SC and ST connectors. Can be used with duplex or simplex cable assemblies.

Features

- Dual SC and ST female connectors
- For 62.5/125 or 50/125 multimode fiber

Specifications

OVERVIEW	
UPC Code	037332120298
Technology	Multimode
CONNECTIONS	
Side A - Connector 1	SC DUPLEX (FEMALE)
Side B - Connector 1	ST DUPLEX (FEMALE)
PHYSICAL	
Color	Light Gray
Number of Fibers	2
Shipping Dimensions (hwd / in.)	0.10 x 7.00 x 9.50
Shipping Dimensions (hwd / cm)	0.25 x 17.78 x 24.13
Shipping Weight (lbs.)	0.04
Shipping Weight (kg)	0.02

Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
ENVIRONMENTAL	
Operating Temperature Range	-4° to 158°F (-20° to 70°C)
Storage Temperature Range	-13° to 176°F (-25° to 80°C)
FEATURES & SPECIFICATIONS	
Push/Pull Tabs	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.