

Spec. Cable Gland M25 Cable-Ø9-17 SBC



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 5013
Specification	Spec. Cable Gland M25 Cable-Ø9-17 SBC
HARTING eCatalogue	https://b2b.harting.com/19000005013

Identification

Category	Accessories
Series of hoods/housings	Han® HPR EasyCon
Type of accessory	Cable gland
Description of the accessory	EMC version

Technical characteristics

Tightening torque	10 Nm
Wrench size	29
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP65 / IP68
Size	M25
Clamping range	9 ... 17 mm
Width across corners	32 mm

Material properties

Material (seal)	EPDM
Material (cable glands)	Brass
Material (clamping ring)	Polyamide (PA)
Surface (accessories)	Nickel plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	1
Net weight	86.75 g
Country of origin	Germany
European customs tariff number	84849000
GTIN	5713140123557
ETIM	EC000441
eCl@ss	27140803 Cable gland EMC (electrical installation)