




- NOTES:
1. ALL PARTS TO BE BULK PACKED.
2. CONTACTS TO BE INSERTED IN CONNECTOR




FACE VIEW
P/N: 6282-2SG-3XX




FACE VIEW
P/N: 6282-3SG-3XX




FACE VIEW
P/N: 6282-4SG-3XX




FACE VIEW
P/N: 6282-5SG-3XX



FACE VIEW
P/N: 6282-6SG-3XX




FACE VIEW
P/N: 6282-7SG-3XX




FACE VIEW
P/N: 6282-8SG-3XX

O-RING
MAT'L: NEOPRENE, BLACK


.040 REF.
[1.0mm]



CABLE CONNECTOR
MAT'L: THERMOPLASTIC, BLACK




COUPLING RING
MAT'L: THERMOPLASTIC, BLACK



SHOWN ASSEMBLED KIT
FOR CUSTOMER REFERENCE ONLY

DIMENSIONS IS BRACKETS [] ARE METRIC

GROMMET, DAISY CHAIN
MAT'L: RUBBER, BLACK
FOR 6282-XSG-3DC




SINGLE GROMMET
MAT'L: RUBBER, BLACK
6282-XSG-311 .125 I.D FOR CABLES .09-.14 [2.3-3.5mm] O.D.
6282-XSG-315 .159 I.D FOR CABLES .15-.17 [3.8-4.3mm] O.D.
6282-XSG-318 .187 I.D FOR CABLES .18-.20 [4.6-5.1mm] O.D.
6282-XSG-321 .225 I.D FOR CABLES .21-.23 [5.3-5.8mm] O.D.

NUMBER OF CONTACTS

GROMMET SIZE FOR
SINGLE GROMMET,
OR "DC" FOR DAISY
CHAIN

ASS'Y P/N	COUP. RING COLOR
6282-XSG-3XXCC1	WHITE
6282-XSG-3XXCC2	RED
6282-XSG-3XXCC3	BLUE
6282-XSG-3XXCC4	LIGHT GREY
6282-XSG-3XXCC5	YELLOW
6282-XSG-3XXCC6	MAROON
6282-XSG-3XXCC7	GREEN



WIRE VIEW
SHOWN 6282-8SG-3XX

BACKSHELL
MAT'L: THERMOPLASTIC, BLACK

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____

DATE: _____

RoHS COMPLIANT

B	SS	11-07-18	ADDED CHART FOR COUPLING RING COLOR PER DOR 18-E149SL #25
A	AN	12-08-16	CONVERTED TO FAMILY DRAWING, ADDED 6282-6SG-3XX, SUPERSEDED 2-5 POS. & 7-8 POS. DRAWINGS. PER DOR 16-E149SL #20
REV.	INIT.	DATE	DESCRIPTION
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			ORIG. DRAWN BY: AN DATE: 12-07-16
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			CHECKED BY: _____
APPROVED BY: _____			TITLE: CABLE CONNECTOR KIT (2-8) #20 SOCKET CONTACTS MINI-CON-X STANDARD PRODUCT
SCALE: NTS	SIZE: B	SHEET: 1 OF 1	CUSTOMER: _____
FILE: 6282-XSG-3XX(CCX)	DIRECTORY: SLW	PART NUMBER: 6282-XSG-3XX(CCX)	REV: B