

M38999/9 Dummy Stowage Receptacle Bayonet Coupling



Dummy Stowage
Receptacles

MATING CONNECTOR

MIL-DTL-38999 Series I

Basic
Part No.

M38999/9

Finish

B = Cadmium Olive Drab
over Electroless Nickel

11

B

Shell Size




TABLE I: Dash Number, Cable Entry
and Backshell Dimensions

Shell Size	E Max		F Dim		G Max		H Nom		J Max		K	
											±.010	(.3)
9	.572	(14.5)	.719	(18.3)	.958	(24.3)	.128	(3.3)	.085	(2.2)	.727	(18.5)
11	.701	(17.8)	.812	(20.6)	1.051	(26.7)	.128	(3.3)	.085	(2.2)	.727	(18.5)
13	.851	(21.6)	.906	(23.0)	1.145	(29.1)	.128	(3.3)	.085	(2.2)	.727	(18.5)
15	.976	(24.8)	.969	(24.6)	1.239	(31.5)	.128	(3.3)	.085	(2.2)	.727	(18.5)
17	1.101	(28.0)	1.062	(27.0)	1.332	(33.8)	.128	(3.3)	.085	(2.2)	.727	(18.5)
19	1.208	(30.7)	1.156	(29.4)	1.458	(37.0)	.128	(3.3)	.085	(2.2)	.727	(18.5)
21	1.333	(33.9)	1.250	(31.8)	1.582	(40.2)	.128	(3.3)	.115	(2.9)	.697	(17.7)
23	1.458	(37.0)	1.375	(34.9)	1.708	(43.4)	.147	(3.7)	.115	(2.9)	.697	(17.7)
25	1.583	(40.2)	1.500	(38.1)	1.832	(46.5)	.147	(3.7)	.115	(2.9)	.697	(17.7)

APPLICATION NOTES

1. Assembly to be identified with manufacturer's name and part number, space permitting.
2. For complete dimensions, see the applicable Military Specification.
3. Metric dimensions (mm) are in parentheses.