





RIB INDICATES
CIRCUIT #1



- 1 MATERIAL: HOUSING-NYLON, UL94V-2 (COLOR-NATURAL, COLOR OF PARTS MAY VARY).
CONTACTS-0.25 [.010] THICK BRASS ALLOY
- 2 CONTACT FINISH: 0.000100 [.0000039] MIN.
MATTE TIN OVER 0.000050 [.0000020] MIN.
NICKEL OVER ENTIRE CONTACT.
- 3 MATES WITH 4.2mm P.E. RECEPTACLE HOUSINGS.

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. <u>S. HOOVER</u> 12-NOV-2004		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
		CHK. <u>D. COLEY</u> 12-NOV-2004			
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME VERTICAL HEADER ASSEMBLY - BLINDMATE WITHOUT DRAIN HOLES, VAL-U-LOK(TM)	
		0 PLC ± .1 1 PLC ± .1 2 PLC ± 0.13 [.005] 4 PLC ± .1 ANGLES FINISH ± 8°/30°			
MATERIAL 		APPLICATION SPEC		SIZE A1 CASE CODE 00779 DRAWING NO C-1586586 RESTRICTED TO	
		WEIGHT		CUSTOMER DRAWING	
				SCALE 5:1 SHEET 1 OF 1 REV A1	