





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/12/21	
A		UPDATE SPEC.	11/12/21	WX/RC



PB7-06LB22FFPXXXXX



LED Ring Color	LED Voltage	
	6V	6V AC/DC
R	Red	6V AC/DC
G	Green	12V AC/DC
Y	Yellow	24V AC/DC
O	Orange	110V AC/DC
B	Blue	220V AC/DC
W	White	220V AC/DC

Current (In)	Non electrical	Inductive load	Inductive load	Inductive load
Voltage UI	Relative load	LED load	Inductive load	Inductive load
AC250	15	2	10	3
DC8	15	4	10	6
DC30	10	4	10	4
DC125	0.6	0.1	0.6	0.1
DC250	0.3	0.05	0.3	0.05

SPECIFICATIONS:

Material:

Body: POM, Rated UL94V-0
Bushing: Stainless Steel
Button: Stainless Steel
Contact Material: Silver Alloy, (4.8mm)
Terminal: Brass, Silver plated

Electrical:

Voltage Rating: 220V
Contact resistance: 50 m Ω max.
Insulation resistance: 1000M ohms min @ 500V DC.
Dielectric withstanding voltage: 1500V RMS, 50Hz.
Electrical Life: 50,000 cycles min at full load.
Temperature Rating:
Operating temperature: -25°C to +55°C
Environmental:
IP65 Front Panel Protection
Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES
X .10
.XX $\pm .020$
.XXX $\pm .015$
HOLES
ØX $\pm .010$
ØXX $\pm .015$
ØXXX $\pm .010$

DRAWN	JJ	11/2/21
CHECKED	RC	11/2/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

ADAM
TECH

TITLE
SWITCH, ANTI-VANDAL, PUSH BUTTON, HIGH CURRENT, SPDT, 19mm, LATCHING, ON-ON

SIZE	PART NO.	REV.
X	PB7-06LB22FFPXXXXX	A

REF: S00198T SCALE: NTS

SHEET 1 OF 1